



## C-MAG MS 10

### /// Data Sheet

Magnetic stirrer without heating. With ceramic set-up plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 15 l (H<sub>2</sub>O)
- Elevated control panel for protection against leaking liquids
- Speed range: 100 - 1500 rpm

#### Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H <sub>2</sub> O) [l]	15
Motor rating output [W]	1.5
Direction of rotation	left
Speed control	scale 0 - 6
Speed range [rpm]	100 - 1500



designed for scientists

Stirring bar length max. [mm]	80
Set-up plate material	ceramic
Set-up plate dimensions [mm]	260 x 260
Dimensions (W x H x D) [mm]	300 x 105 x 415
Weight [kg]	6
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230 / 120 / 100
Frequency [Hz]	50/60
Power input [W]	30

